

Kodak 1500

Intraoral Camera

The ideal communication starter

The Kodak 1500 intraoral camera is the ideal communication tool for any dental practitioner. Delivering precise, true-to-life images with each shot, the Kodak 1500 camera provides the powerful visual evidence you need to educate patients and make more accurate diagnoses. Now you can let patients see exactly what you see – so they make smarter decisions, and are more likely to accept treatment.

Industry-leading resolution and focus range

Boasting the industry's highest still image resolution, the Kodak 1500 camera provides all the functions you need to capture sharp, clear color images. And with the widest focus range available (1mm to infinity), practitioners can clearly view even the smallest details – making diagnosis and treatment planning easier and more accurate than ever.

Portable and economical

USB technology lets you share the Kodak 1500 camera between several treatment rooms, which means you can use it anytime and anywhere you need it. Simply plug the camera straight into your computer, and you're ready to work – no docking station required. In seconds, you can view the images on your monitor and store them on your hard drive. It's the easiest way to access and share patient images.

Effortless image capture

The Kodak 1500 camera's one-button image capture allows anyone on your team to capture clear, detailed images quickly and easily.



Combined with a true autofocus, the camera's unique liquid lens technology works like the human eye to ensure clear, detailed images each and every time.



The Kodak 1500 camera features:

- True autofocus with liquid lens technology
- Best-in-class resolution and focus range
- Auto adjustable white LED lighting for optimized and bright illumination
- One-button simplicity
- Available in two wired configurations – with or without docking station



Flexible, all-purpose design

The Kodak 1500 camera is a versatile tool for any dental practice. With just one camera, you can capture still images and fluid videos, perform both intra- and extraoral exams, and quickly display images on your choice of a PC or video monitor. And, with three configurations available – wireless, wired with docking station, or a wired USB version, the Kodak 1500 camera is designed to meet the specific needs of any dental practice.

Simply integrated

Easily modify, store, and manage your images and videos with the included Kodak dental imaging software. Simply press the acquisition button to capture a still image and it's automatically saved to your computer or SD card. Images can then be integrated into patient files, printed, and shared.

Reliable services and support

We provide the guidance and support you need to get the most out of your Kodak 1500 camera. Our experienced support experts are here to help you integrate your camera into your practice and are available to answer your questions before, during, and after your purchase.



TECHNICAL SPECIFICATIONS

Sensor:	Micron 1/2.5" CMOS 2592 (H) x 1944 (V)
Video resolution:	640 (H) x 480 (V)
Image resolution:	1024 (H) x 768 (V)
Focus range:	1mm to infinity
Angle of view:	90°
Field of view:	80°
Focus:	Autofocus
Light source:	8 White LED array
Video output:	USB 2.0; TV-NTSC; TV-PAL; VGA; S-Video
Connection:	USB 2.0 high-speed interface



Would you like to know more?

www.carestreamdental.com

Alternatively, contact your local authorized dealer.

Want to subscribe to our newsletter?

E-mail dentalnews@carestream.com.



Carestream Dental

©Carestream Health, Inc. 2010.

The Kodak trademark and trade dress are used under license from Kodak.

10/01/10