

Kodak 1500

Intraoral Video Camera

The latest intraoral imaging technology

The Kodak 1500 intraoral camera is the ideal communication tool for any dental practitioner. Elegantly styled and easy to use, Kodak's first wireless intraoral camera delivers stunning images with the convenience and freedom of Wi-Fi connectivity.

Easy-to-use

The Kodak 1500 camera's intuitive design includes a true autofocus and an automatic light source to help you obtain all the views you need - no manual adjustments required. And convenient features such as an acquisition button located directly on the camera ensure easy manipulation and quick image capture.

Wireless freedom

With built-in Wi-Fi support, the Kodak 1500 camera provides total freedom of movement. Using the power of wireless, the camera intuitively transfers information between the handpiece and docking station - no wired connection required. And USB connectivity enables you to share the docking station between several treatment rooms, which means you can use the camera anytime and anywhere you need it.

Superb image quality

Ideal for both intraoral and extraoral images, the Kodak 1500 camera provides all the functions you need to capture clear, true-to-life color views that can be more accurately communicated with patients. The eight-point LED light ensures exceptional color and quality while the autofocus feature helps you capture the perfect shot without ever having to adjust the camera.



The KODAK 1500 Camera features:

- Patented true autofocus technology
- Wireless camera for cable-free connection
- White LED lighting for uniform and bright illumination
- Intraoral and extraoral views
- Compatible with both computer and video monitors



Flexible, all-purpose design

An affordable solution for any dental practice, the Kodak 1500 camera is a versatile tool that has many applications. With just one camera, you can capture still images and fluid videos, perform both intra- and extraoral exams, and quickly display images on your choice of a PC or video monitor.

Seamless integration

Easily modify, store and manage your images and video with the included Kodak dental imaging software. Simply press the acquisition button to capture a still image and it's automatically saved to your computer or SD card. Images can then be integrated into patient files, printed and shared.

Reliable services and support


We provide the guidance and support you need to get the most out of your Kodak 1500 camera. Our experienced support experts are here to help you integrate your camera into your practice and are available to answer your questions before, during and after your purchase.



TECHNICAL SPECIFICATIONS

Sensor:	Micron 1/2.5" CMOS 2592 (H) x 1944 (V)
Video resolution:	640 (H) x 480 (V)
Image resolution:	1280 (H) x 960 (V)
Focus range:	1 mm to infinity
Angle of field:	80°
Focus:	Autofocus
Light source:	8 White LED array
Video output:	USB 2.0; TV-NTSC; TV-PAL; VGA; S-Video
Connection:	USB 2.0 high-speed interface

Wireless technology: Wi-Fi (only available with the wireless version)



To schedule a demonstration or to receive further information, please contact your authorized dealer.



Carestream Health

©Carestream Health, Inc. 2009.
The Kodak trademark and trade dress are used under license from Kodak.

03/09/09